



Push-pull toggle clamp with angled base, Type: 2



Order data

Order number	376710 2
GTIN	4020772008413
Item class	35A

Description

Version:

With **compound action**. Opening prevented by self-locking mechanism.

- **Rivet made of stainless steel, bearings greased.**
- **With long push-pull guide.**
- **Handle can be moved to any angle.**
- **With hardened and galvanised contact screw.**
- **Detachable angled base, permitting fixing to sheet metal walls.**

Application:

For use in special clamping fixtures for drilling, reaming, grinding, bending, welding, fitting etc.

Optional extras:

Angled base No. 376730.

Note:

- **Size 0 and 3 also available in stainless steel!**

Technical description

Clamping force P (pressure and traction)	2000 N
Bore \varnothing d	5.6 mm
thread at front of clamp	M16×1.5 mm

Contact screw	M6×25 mm
Clamping range	26 mm
Angled base width K	50 mm
Hole spacing f	31.8 - 36 mm
Clamping height b to centre of screw	20 mm
Overall height H	85.5 mm
Overall length L	244 mm
Type	6841J
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 2	376730 2
Angled base sturdy Type 5	376730 5
Angled base sturdy Type 3	376730 3