



Horizontal toggle clamp with angled base, Type: 2



Order data

Order number	376640 2
GTIN	4020772008277
Item class	35A

Description

Version:

Captive contact screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

With angled base for side attachment.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Bore \varnothing d	5.6 mm
Hole spacing f	25.5 mm
overall height	94 mm
Clamping force P1	1000 N
Clamping force P2	1200 N
Hole spacing e	20 mm

Contact screw	M6×35 mm
overall length	162 mm
Type	6833J
Clamping height H	48 mm
Type of product	Horizontal toggle clamp