



Vertical toggle clamp with horizontal base, Type: 1



Order data

| | |
|--------------|---------------|
| Order number | 376508 1 |
| GTIN | 4045197226266 |
| Item class | 32S |

Description

Version:

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

| | |
|----------------------|---------|
| Hole spacing e | 16 mm |
| overall length | 51.5 mm |
| Clamping force P1 | 500 N |
| Clamping force P2 | 710 N |
| Bore \varnothing d | 3 mm |
| overall height | 77 mm |

| | |
|-------------------|------------------------|
| Hole spacing f | 24 mm |
| Contact screw | M5×30 mm |
| Type | 376508 1 |
| Clamping height H | 19 mm |
| Type of product | Vertical toggle clamps |