



Push-pull toggle clamp with angled base, Type: 3



Order data

Order number	376710 3
GTIN	4020772008420
Item class	35A

Description

Version:

With **compound action**. Opening prevented by self-locking mechanism.

- **Rivet made of stainless steel, bearings greased.**
- **With long push-pull guide.**
- **Handle can be moved to any angle.**
- **With hardened and galvanised contact screw.**
- **Detachable angled base, permitting fixing to sheet metal walls.**

Application:

For use in special clamping fixtures for drilling, reaming, grinding, bending, welding, fitting etc.

Optional extras:

Angled base No. 376730.

Note:

- **Size 0 and 3 also available in stainless steel!**

Technical description

Clamping height b to centre of screw	25 mm
Clamping force P (pressure and traction)	2500 N
Clamping range	32 mm

thread at front of clamp	M20×1.5 mm
Bore Ø d	6.5 mm
Contact screw	M8×35 mm
Angled base width K	60 mm
Hole spacing f	29.5 - 42.5 mm
Overall height H	108 mm
Overall length L	302.5 mm
Type	6841J
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 2	376730 2
Angled base sturdy Type 5	376730 5
Angled base sturdy Type 3	376730 3