



Vertical toggle clamp with horizontal base, Type: 2



Order data

Order number	376508 2
GTIN	4045197226273
Item class	32S

Description

Version:

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping force P1	1200 N
Contact screw	M6×50 mm
overall height	140 mm
Hole spacing e	12,5 mm
Bore Ø d	5.2 mm
Clamping force P2	1500 N

Hole spacing f	27 mm
overall length	74.5 mm
Type	376508 2
Clamping height H	22.5 mm
Type of product	Vertical toggle clamps