



## Vertical toggle clamp with angled base for side attachment, Type: 3



### Order data

Order number	376520 3
GTIN	4020772007904
Item class	35A

### Description

#### Version:

With angled base for side attachment.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**
- **Captive contact screw.**
- **Finger protection thanks to safety clamping mechanism no trap points.**

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

overall height	223 mm
Clamping force P1	1400 N
overall length	111 mm
Hole spacing f	28.5 mm

Hole spacing e	24 mm
Bore Ø d	6.5 mm
Contact screw	M8×45 mm
Clamping force P2	2500 N
Type	6803J
Clamping height H	40 mm
Type of product	Vertical toggle clamps