



Horizontal toggle clamp with horizontal base, Type: 3



Order data

| | |
|--------------|---------------|
| Order number | 376610 3 |
| GTIN | 4020772008086 |
| Item class | 35A |

Description

Version:

Captive contact screws.

Compact design due to new handle.

Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

| | |
|----------------------|------------|
| Clamping force P1 | 1800 N |
| Hole spacing f | 22-31.8 mm |
| Contact screw | M8x45 mm |
| Hole spacing e | 25.7 mm |
| Bore \varnothing d | 6.5 mm |
| overall height | 48.5 mm |
| Clamping force P2 | 2500 N |

| | |
|-------------------|-------------------------|
| overall length | 206 mm |
| Type | 6830J |
| Clamping height H | 32 mm |
| Type of product | Horizontal toggle clamp |