

**Garant****Stainless straight edge in a case, Length: 300mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 460095 300    |
| GTIN         | 4045197444318 |
| Item class   | 41H           |

**Description****Version:**

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of **stainless steel**. **Both bevels anti-glare matt finished.**

**Note:**

The straightness tolerance of the measuring edge refers to a displacement range of  $\pm 15^\circ$  to the symmetry plane.

**Technical description**

|  |                       |
|--|-----------------------|
| Straightness tolerance of the measuring edge | 0.003 mm              |
| Length                                       | 300 mm                |
| Standard                                     | DIN 874               |
| Material                                     | stainless steel       |
| Surface chamfer                              | non-glare matt finish |
| Packaging                                    | Wallet                |
| Calibration                                  | F6                    |
| Type of product                              | Straight edge         |

**Services**

|  |            |
|--|------------|
| DAkkS calibrationStraight edge maximum length 500 mm | 026010 500 |
|--|------------|

CalibrationStraight edge maximum length 500 mm

026000 500