



## Push-pull toggle clamp with angled base, Type: 5



### Order data

Order number	376710 5
GTIN	4020772008437
Item class	35A

### Description

#### Version:

With **compound action**. Opening prevented by self-locking mechanism.

- **Rivet made of stainless steel, bearings greased.**
- **With long push-pull guide.**
- **Handle can be moved to any angle.**
- **With hardened and galvanised contact screw.**
- **Detachable angled base, permitting fixing to sheet metal walls.**

#### Application:

For use in special clamping fixtures for drilling, reaming, grinding, bending, welding, fitting etc.

#### Optional extras:

Angled base No. 376730.

#### Note:

- **Size 0 and 3 also available in stainless steel!**

### Technical description

Clamping range	40 mm
Hole spacing f	29 - 46 mm
thread at front of clamp	M24×1,5 mm

Bore Ø d	8.5 mm
Clamping force P (pressure and traction)	4500 N
Clamping height b to centre of screw	30 mm
Angled base width K	65 mm
Contact screw	M12×50 mm
Overall height H	129.5 mm
Overall length L	379.5 mm
Type	6841J
Type of product	Push-pull toggle clamp

---

## Accessories

Angled base sturdy Type 2	376730 2
Angled base sturdy Type 5	376730 5
Angled base sturdy Type 3	376730 3