




Horizontal toggle clamp with angled base, Type: 4



Order data

Order number	376640 4
GTIN	4020772008291
Item class	35A

Description

Version:

Captive contact screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

With angled base for side attachment.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

overall height	133 mm
Hole spacing f	32 mm
Clamping force P1	2000 N
Clamping force P2	3000 N
Contact screw	M8×65 mm
overall length	282 mm

Bore Ø d	8.5 mm
Hole spacing e	32 mm
Type	6833J
Clamping height H	60 mm
Type of product	Horizontal toggle clamp