

Garant**Stainless straight edge in a case, Length: 500mm****Order data**

Order number	460095 500
GTIN	4045197444325
Item class	41H

Description**Version:**

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of **stainless steel**. **Both bevels anti-glare matt finished.**

Note:

The straightness tolerance of the measuring edge refers to a displacement range of $\pm 15^\circ$ to the symmetry plane.

Technical description

Straightness tolerance of the measuring edge	0.004 mm
Length	500 mm
Standard	DIN 874
Material	stainless steel
Surface chamfer	non-glare matt finish
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

Services

CalibrationStraight edge maximum length 500 mm	026000 500
--	------------

DAkKS calibrationStraight edge maximum length 500 mm

026010 500