




Horizontal toggle clamp with horizontal base, Type: 4



Order data

Order number	376625 4
GTIN	4045197229946
Item class	32S

Description

Version:

Captive contact screws.

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

overall height	90 mm
Bore \varnothing d	8.8 mm
Hole spacing f	43 mm
Clamping force P1	2500 N
Clamping force P2	3500 N
Contact screw	M10×90 mm
Hole spacing e	41.2 mm
overall length	273 mm
Type	376625 4

Clamping height H	45 mm
Type of product	Horizontal toggle clamp