



## Push-pull toggle clamp with hand lever (can be pulled-out), Type: 5



### Order data

Order number	376760 5
GTIN	4020772092641
Item class	35A

### Description

#### Version:

- **Very sturdy design, with slide-ram guide.**
- **Slide-ram and hand lever move together.**
- **Body of malleable cast iron.**
- **Lever parts and slide ram made of quenched and tempered steel, galvanised and passivated.**
- **Hardened contact screw.**
- **Hardened bolts, maintenance-free sintered bushes.**
- **For high clamping forces.**
- **Body of malleable cast iron, burnished.**

#### Application:

- **For quick clamping / releasing in series production.**
- **As push or pull clamp.**
- **For incorporation within special jigs and fixtures.**
- **Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.**

### Technical description

Base body width n	58 mm
-------------------	-------

Clamping height b to centre of screw	18 mm
Hole spacing m	41 mm
Hole spacing g	41 mm
Bore Ø d	8.5 mm
Hole spacing l	35 mm
Clamping force P (pressure and traction)	12000 N
Base body length f	137 mm
Contact screw	M10×50 mm
Hole spacing k	8 mm
Weight	1.65 kg
Clamping range	50 mm
Overall height H	210 mm
Overall length L	250 mm
Type	6842PL
Type of product	Push-pull toggle clamp