



## Horizontal toggle clamp with safety-locking mechanism, Type: 3



### Order data

Order number	376650 3
GTIN	4020772008819
Item class	35A

### Description

#### Version:

- Rivet made of stainless steel.
- Case-hardened bearing bushes.
- Bearings greased.
- Complete with hardened and galvanised contact screw.
- More compact design due to new handle.
- Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.
- Captive contact screws.

#### Application:

Particularly suitable for use where vibrations occur and for overhead applications due to patented safety-locking in closed and open state.

### Technical description

Clamping force P1	1800 N
Hole spacing f	22-31.8 mm
Hole spacing e	25.7 mm
overall height	48.5 mm
Clamping force P2	2500 N
Contact screw	M8×45 mm

overall length	206 mm
Bore Ø d	6.5 mm
Type	6830SJ
Clamping height H	32 mm
Type of product	Horizontal toggle clamp