



Straight edge with burnished finish in a case, Length: 75mm



Order data

Order number	460100 75
GTIN	4045197206503
Item class	42G

Description

Version:

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of aged special steel, both bevels burnished (anti-glare).

Note:

The straightness tolerance of the measuring edge refers to a displacement range of $\pm 15^\circ$ to the symmetry plane.

Technical description

Length	75 mm
Straightness tolerance of the measuring edge	0.002 mm
Standard	DIN 874
Material	aged special steel
Surface chamfer	burnished (non-glare)
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

Services

CalibrationStraight edge maximum length 200 mm	026000 200
--	------------

DAkkS calibration Straight edge maximum length 500 mm

026010 500