



Horizontal toggle clamp with vertical base, Type: 0



Order data

Order number	376630 0
GTIN	4020772008154
Item class	35A

Description

Version:

Captive contact screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

With vertical base for fixing to ribs and for welded structures.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

overall height	33 mm
Bore \varnothing d	4.6 mm
Contact screw	M4x25 mm
Hole spacing e	11.5-15.5 mm
Clamping force P2	400 N
Clamping force P1	250 N
overall length	79 mm

Type	6832J
Clamping height H	20 mm
Type of product	Horizontal toggle clamp