



## Push-pull toggle clamp with hand lever (can be pulled-out), Type: 7



### Order data

Order number	376760 7
GTIN	4020772092665
Item class	35A

### Description

#### Version:

- **Very sturdy design, with slide-ram guide.**
- **Slide-ram and hand lever move together.**
- **Body of malleable cast iron.**
- **Lever parts and slide ram made of quenched and tempered steel, galvanised and passivated.**
- **Hardened contact screw.**
- **Hardened bolts, maintenance-free sintered bushes.**
- **For high clamping forces.**
- **Body of malleable cast iron, burnished.**

#### Application:

- **For quick clamping / releasing in series production.**
- **As push or pull clamp.**
- **For incorporation within special jigs and fixtures.**
- **Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.**

### Technical description

Weight	4.28 kg
--------	---------

Clamping force P (pressure and traction)	25000 N
Bore Ø d	10.5 mm
Base body length f	198 mm
Hole spacing k	12 mm
Hole spacing g	54 mm
Contact screw	M12×50 mm
Hole spacing l	45 mm
Clamping height b to centre of screw	22 mm
Hole spacing m	45 mm
Clamping range	75 mm
Base body width n	84 mm
Overall height H	285 mm
Overall length L	355 mm
Type	6842PL
Type of product	Push-pull toggle clamp