



## Horizontal toggle clamp with safety-locking mechanism, Type: 4



### Order data

Order number	376650 4
GTIN	4020772008826
Item class	35A

### Description

#### Version:

- Rivet made of stainless steel.
- Case-hardened bearing bushes.
- Bearings greased.
- Complete with hardened and galvanised contact screw.
- More compact design due to new handle.
- Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.
- Captive contact screws.

#### Application:

Particularly suitable for use where vibrations occur and for overhead applications due to patented safety-locking in closed and open state.

### Technical description

Hole spacing e	41 mm
Clamping force P2	3000 N
Hole spacing f	29-43 mm
overall height	75 mm
overall length	287 mm
Contact screw	M8x65 mm

Bore Ø d	8.5 mm
Clamping force P1	2000 N
Type	6830SJ
Clamping height H	45 mm
Type of product	Horizontal toggle clamp