



## Horizontal toggle clamp with vertical base, Type: 1



### Order data

Order number	376630 1
GTIN	4020772008161
Item class	35A

### Description

#### Version:

Captive contact screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

With vertical base for fixing to ribs and for welded structures.

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

Contact screw	M5×30 mm
Clamping force P1	800 N
Clamping force P2	1100 N
overall height	43 mm
Bore Ø d	5.2 mm
Hole spacing e	13-14.5 mm
overall length	120 mm

Type	6832J
Clamping height H	25.5 mm
Type of product	Horizontal toggle clamp