



Horizontal toggle clamp with horizontal base, stainless, Type: 0



Order data

Order number	376620 0
GTIN	4020772008932
Item class	35A

Description

Version:

Captive contact screws.

Compact design due to new handle.

Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping force P2	400 N
overall length	79 mm
Hole spacing e	11.5-14.5 mm
Contact screw	M4×25 mm
Hole spacing f	16 mm
overall height	23 mm
Bore Ø d	4.6 mm

Clamping force P1	250 N
Type	6830NIJ
Clamping height H	14.5 mm
Type of product	Horizontal toggle clamp