



Heavy push-pull toggle clamp, Type: 5



Order data

Order number	376720 5
GTIN	4020772008581
Item class	35A

Description

Version:

- Very sturdy design, with slide-ram guide.
- Slide-ram and hand lever move together.
- Body of malleable cast iron.
- Lever parts and slide ram made of quenched and tempered steel, galvanised and passivated.
- Hardened contact screw.

Application:

- For quick clamping / releasing in series production.
- As push or pull clamp.
- For incorporation within special jigs and fixtures.
- Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Clamping height b to centre of screw	38 mm
Clamping range	40 mm
Hole spacing e	41 mm
Hole spacing g	41 mm

Hole spacing f	50 mm
Bore Ø d	8.5 mm
Clamping force P (pressure and traction)	10000 N
Contact screw	M12×50 mm
Overall height H	137.5 mm
Overall length L	380 mm
Type	6842
Type of product	Push-pull toggle clamp