



## Push-pull toggle clamp short body, Type: 2



### Order data

Order number	376700 2
GTIN	4020772008543
Item class	35A

### Description

#### Version:

Hardened shoulder screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

#### Application:

- **Direct fixing to sheet metal fixing points.**
- **Connected to jig body with threaded end of arm.**

#### Optional extras:

Angled base No. 376730.

#### Note:

- **Available in stainless steel on request.**

### Technical description

thread at front of clamp	M16×1.5 mm
Contact screw	M6×25 mm
Clamping range	21.5 mm

Clamping force P (pressure and traction)	1000 N
Overall height H	73 mm
Overall length L	161.5 mm
Type	6844J
Type of product	Push-pull toggle clamp

---

## Accessories

Angled base sturdy Type 3	376730 3
Angled base sturdy Type 5	376730 5
Angled base sturdy Type 2	376730 2