

TAJIMA

Steel rule, stainless, Length: 300 mm



Order data

Order number	461620 300
GTIN	4975364041210
Item class	46R

Description

Version:

Stainless steel, matt surface with sharp contrast graduations.

Upper edge mm graduations, lower 1/2 mm graduations.

Rear with inch/ metric conversion table and table of tapping drill \varnothing .

Material: Stainless steel, INOX

Calibration: F10

Error limit: 0.13 mm

Cross-section width: 25 mm

Cross-section thickness: 1 mm

Technical description

Length	300 mm
Cross-section width	25 mm
Cross-section thickness	1 mm
Calibration	F10
Error limit	0.13 mm
Standard	EG I
Graduation on the top edge	1 mm
Graduation on the bottom edge	1/2 mm
Material	Stainless steel, INOX
Type of product	Steel rule

Services

Calibration Steel scale maximum length 500/2 mm	016100 500/2
Labelling laser-etched Type	018940