



Horizontal toggle clamp with vertical base, Type: 2



Order data

Order number	376630 2
GTIN	4020772008185
Item class	35A

Description

Version:

Captive contact screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

With vertical base for fixing to ribs and for welded structures.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Bore \varnothing d	5.6 mm
overall height	61 mm
Hole spacing e	26 mm
Clamping force P2	1200 N
Contact screw	M6x35 mm
Clamping force P1	1000 N
overall length	164 mm

Type	6832J
Clamping height H	34 mm
Type of product	Horizontal toggle clamp