



## Horizontal toggle clamp with horizontal base, stainless, Type: 1



### Order data

Order number	376620 1
GTIN	4020772008949
Item class	35A

### Description

#### Version:

Captive contact screws.

Compact design due to new handle.

Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.

With horizontal base for fixing to base plates etc.

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

Bore $\varnothing$ d	5.2 mm
overall height	30 mm
overall length	120 mm
Clamping force P1	800 N
Contact screw	M5x30 mm
Clamping force P2	1100 N
Hole spacing e	13-14.5 mm

Hole spacing f	19.7 mm
Type	6830NIJ
Clamping height H	19 mm
Type of product	Horizontal toggle clamp