



Hook toggle clamp with clamping hook, Type: 1



Order data

Order number	376740 1
GTIN	4020772094522
Item class	35A

Description

Version:

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

Application:

For closing containers.

Technical description

Hole spacing e	19 mm
Clamping force P (traction)	2000 N
Bore \varnothing d	5.4 mm
Adjustment travel of clamping hook c	35 - 42 mm
Hole spacing f	26 - 30 mm
Thickness a	5.3 mm
Radius R	4.5 mm

Clamping height h	22.7 mm
Overall height H	34.5 mm
Overall length L	104.6 mm
Type	6847
Type of product	Hook toggle clamp