



## Heavy push-pull toggle clamp, Type: 7



### Order data

Order number	376720 7
GTIN	4020772008598
Item class	35A

### Description

#### Version:

- Very sturdy design, with slide-ram guide.
- Slide-ram and hand lever move together.
- Body of malleable cast iron.
- Lever parts and slide ram made of quenched and tempered steel, galvanised and passivated.
- Hardened contact screw.

#### Application:

- For quick clamping / releasing in series production.
- As push or pull clamp.
- For incorporation within special jigs and fixtures.
- Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

### Technical description

Clamping height b to centre of screw	55 mm
Hole spacing f	65 mm
Clamping range	50 mm
Hole spacing g	57 mm

Clamping force P (pressure and traction)	25000 N
Bore Ø d	11 mm
Hole spacing e	70 mm
Contact screw	M12×50 mm
Overall height H	179 mm
Overall length L	460 mm
Type	6842
Type of product	Push-pull toggle clamp