

TAJIMA

Steel rule, stainless, Length: 600 mm



Order data

Order number	461620 600
GTIN	4975364041227
Item class	46R

Description

Version:

Stainless steel, matt surface with sharp contrast graduations.

Upper edge mm graduations, lower 1/2 mm graduations.

Rear with inch/ metric conversion table and table of tapping drill \varnothing .

Material: Stainless steel, INOX

Calibration: F10

Error limit: 0.16 mm

Cross-section width: 30 mm

Cross-section thickness: 1.2 mm

Technical description

Length	600 mm
Cross-section thickness	1.2 mm
Cross-section width	30 mm
Calibration	F10
Error limit	0.16 mm
Standard	EG I
Graduation on the top edge	1 mm
Graduation on the bottom edge	1/2 mm
Material	Stainless steel, INOX
Type of product	Steel rule

Services

Calibration Steel scale maximum length 1000/2 mm	016100 1000/2
Labelling laser-etched Type	018940