



## Hook toggle clamp with clamping hook, Type: 3



### Order data

Order number	376740 3
GTIN	4020772094546
Item class	35A

### Description

#### Version:

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

#### Application:

For closing containers.

### Technical description

Thickness a	7.1 mm
Hole spacing f	31.5 - 35.5 mm
Bore $\varnothing$ d	5.5 mm
Adjustment travel of clamping hook c	72 - 84 mm
Clamping force P (traction)	3000 N
Hole spacing e	19 mm
Radius R	5.5 mm

Clamping height h	22.7 mm
Overall height H	36 mm
Overall length L	200.5 mm
Type	6847
Type of product	Hook toggle clamp