



Horizontal toggle clamp with horizontal base, stainless, Type: 2



Order data

Order number	376620 2
GTIN	4020772008956
Item class	35A

Description

Version:

Captive contact screws.

Compact design due to new handle.

Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

Hole spacing e	26 mm
Clamping force P2	1200 N
Clamping force P1	1000 N
Bore \varnothing d	5.6 mm
Hole spacing f	19.5-29.5 mm
overall height	45 mm
overall length	162 mm

Contact screw	M6×35 mm
Type	6830NIJ
Clamping height H	24 mm
Type of product	Horizontal toggle clamp