



Internal micrometer MicroGauge, Measuring range: 2,25-4,25mm



Order data

Order number	428670 2,25-4,25
GTIN	5051102218942
Item class	46B

Description

Version:

2-point bore measuring system for high-precision measurement of bores between 0.95 – 10.35 mm. The compact format and low weight (no more than a ball-point pen) facilitates measurement of small precision components. Hard chrome plated spherical measurement contacts. Clear LCD display with switchable resolution down to 0.0005 mm. Data output via RS232 or USB proximity. Dust-tight and proof against jets of water (IP65).

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

With 1 battery No. 081560 357, setting rings with UKAS calibration certificates.

Optional extras:

Data cable No. 498948

Note:

Available as individual micrometers or as a set, depth stops available on request. Diatest probes can be connected using an additional adapter.

Technical description

Repeatability	0.001 mm
Number of setting rings	7
Measuring range of the micrometer head	2.25–2.75; 2.5–3; 2.75–3.25; 3–3.5; 3.25–3.75 ; 3.5–4 ; 3.75–4.25 mm
Linearity	Ø 1.0 – 1.55: maximum 2% of the measurement travel; at least 0.001/Ø 1.5 – 6.35: maximum 1% of the measurement travel; at least 0.001 mm
Number of measuring heads	7
Selectable display	0.01/0.001/0.0005 mm
Measuring range	2.25 - 4.25 mm
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	Price on request
Type of product	2-point internal micrometer

Accessories

Button cell / special battery Battery type 357	081560 357
Connection cable Type USB2	498948 USB2
Connection cable Type R2	498948 R2