



Horizontal toggle clamp with vertical base, Type: 3



Order data

Order number	376630 3
GTIN	4020772008192
Item class	35A

Description

Version:

Captive contact screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

With vertical base for fixing to ribs and for welded structures.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Technical description

overall height	65 mm
Clamping force P1	1800 N
overall length	206 mm
Hole spacing e	25.7 mm
Bore \varnothing d	6.5 mm
Contact screw	M8x45 mm
Clamping force P2	2500 N

Type	6832J
Clamping height H	42.5 mm
Type of product	Horizontal toggle clamp