



Hook toggle clamp horizontal, Type: 3



Order data

Order number	376800 3
GTIN	4020772008604
Item class	35A

Description

Version:

Complete with catch.

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

Application:

For closing containers.

Note:

- **More compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

Technical description

Adjustment travel of clamping hook c	48.5 - 96 mm
Bore \varnothing d	6.5 mm

Hole spacing f	24.5 - 32 mm
Hole spacing e	19 mm
Clamping force P (traction)	3200 N
Clamping height h	19 mm
Overall height H	70 mm
Overall length L	169 - 216 mm
Type	6848HJ
Type of product	Hook toggle clamp