

HOLEX**Push-pull toggle clamp short body, Type: 2****Order data**

Order number	376725 2
GTIN	4045197226785
Item class	32S

Description**Version:**

Hardened shoulder screws.

- **Ergonomic handle made of oil-resistant plastic.**

Application:

- **Direct fixing to sheet metal fixing points.**
- **Connected to jig body with threaded end of arm.**

Optional extras:

Angled base No. 376735.

Note:

- **Available in stainless steel on request.**

Technical description

Clamping force P (pressure and traction)	900 N
thread at front of clamp	M16×1.5 mm
Clamping range	19 mm
Contact screw	M6×40 mm
Overall height H	74 mm
Overall length L	163 mm

Type	376725 2
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 3	376735 3
Angled base sturdy Type 2	376735 2