

**HOLEX****Push-pull toggle clamp short body, Type: 2****Order data**

Order number	376725 2
GTIN	4045197226785
Item class	32S

**Description****Version:**

Hardened shoulder screws.

- **Ergonomic handle made of oil-resistant plastic.**

**Application:**

- **Direct fixing to sheet metal fixing points.**
- **Connected to jig body with threaded end of arm.**

**Optional extras:**

Angled base No. 376735.

**Note:**

- **Available in stainless steel on request.**

Clamping range: 19 mm

Clamping force P (pressure and traction): 900 N

Overall height H: 74 mm

Overall length L: 163 mm

Contact screw: M6×40 mm

thread at front of clamp: M16×1.5 mm

**Technical description**

Clamping force P (pressure and traction)	900 N
thread at front of clamp	M16×1.5 mm

Clamping range	19 mm
Contact screw	M6×40 mm
Overall height H	74 mm
Overall length L	163 mm
Type	376725 2
Type of product	Push-pull toggle clamp

---

## Accessories

Angled base sturdy Type 3	376735 3
Angled base sturdy Type 2	376735 2