



Push-pull toggle clamp short body, Type: 5



Order data

Order number	376700 5
GTIN	4020772008567
Item class	35A

Description

Version:

Hardened shoulder screws.

- **Compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

Application:

- **Direct fixing to sheet metal fixing points.**
- **Connected to jig body with threaded end of arm.**

Optional extras:

Angled base No. 376730.

Note:

- **Available in stainless steel on request.**

Technical description

Contact screw	M12×50 mm
thread at front of clamp	M24×1,5 mm
Clamping force P (pressure and traction)	4000 N

Clamping range	67 mm
Overall height H	149 mm
Overall length L	364 mm
Type	6844J
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 5	376730 5
Angled base sturdy Type 2	376730 2
Angled base sturdy Type 3	376730 3