

**Straight edge with burnished finish in a case, Length: 200mm****Order data**

Order number	460100 200
GTIN	4045197206541
Item class	42G

Description**Version:**

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of aged special steel, both bevels burnished (anti-glare).

Note:

The straightness tolerance of the measuring edge refers to a displacement range of $\pm 15^\circ$ to the symmetry plane.

Technical description

Length	200 mm
Straightness tolerance of the measuring edge	0.003 mm
Standard	DIN 874
Material	aged special steel
Surface chamfer	burnished (non-glare)
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

Services

DAkkS calibrationStraight edge maximum length 500 mm	026010 500
--	------------

CalibrationStraight edge maximum length 200 mm

026000 200