



Hook toggle clamp horizontal, Type: 4



Order data

Order number	376800 4
GTIN	4020772008628
Item class	35A

Description

Version:

Complete with catch.

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

Application:

For closing containers.

Note:

- **More compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

Technical description

Hole spacing f	35 - 46 mm
Clamping force P (traction)	7000 N

Adjustment travel of clamping hook c	59 - 123 mm
Bore \varnothing d	8.5 mm
Hole spacing e	32 mm
Clamping height h	26 mm
Overall height H	94.5 mm
Overall length L	209 - 273 mm
Type	6848HJ
Type of product	Hook toggle clamp