



Hook toggle clamp with clamping hook, Type: 5



Order data

Order number	376740 5
GTIN	4020772094560
Item class	35A

Description

Version:

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

Application:

For closing containers.

Technical description

Hole spacing e	29 mm
Bore \varnothing d	11.2 mm
Thickness a	10.75 mm
Hole spacing f	55.5 - 63 mm
Clamping force P (traction)	5000 N
Adjustment travel of clamping hook c	58 - 73 mm
Radius R	8 mm

Clamping height h	49 mm
Overall height H	69 mm
Overall length L	260.5 mm
Type	6847
Type of product	Hook toggle clamp