



Push-pull toggle clamp with angled base, Type: 0



Order data

| | |
|--------------|---------------|
| Order number | 376710 0 |
| GTIN | 4020772008376 |
| Item class | 35A |

Description

Version:

With **compound action**. Opening prevented by self-locking mechanism.

- **Rivet made of stainless steel, bearings greased.**
- **With long push-pull guide.**
- **Handle can be moved to any angle.**
- **With hardened and galvanised contact screw.**
- **Detachable angled base, permitting fixing to sheet metal walls.**

Application:

For use in special clamping fixtures for drilling, reaming, grinding, bending, welding, fitting etc.

Optional extras:

Angled base No. 376730.

Note:

- **Size 0 and 3 also available in stainless steel!**

Technical description

| | |
|--|----------|
| Clamping force P (pressure and traction) | 800 N |
| thread at front of clamp | M10x1 mm |
| Contact screw | M4x20 mm |

| | |
|--------------------------------------|------------------------|
| Clamping range | 16 mm |
| Clamping height b to centre of screw | 12 mm |
| Bore \varnothing d | 4.5 mm |
| Angled base width K | 25 mm |
| Hole spacing f | 16 mm |
| Overall height H | 49.3 mm |
| Overall length L | 140.5 mm |
| Type | 6841J |
| Type of product | Push-pull toggle clamp |

Accessories

| | |
|---------------------------|----------|
| Angled base sturdy Type 2 | 376730 2 |
| Angled base sturdy Type 5 | 376730 5 |
| Angled base sturdy Type 3 | 376730 3 |