

HOLEX**Push-pull toggle clamp short body, Type: 3****Order data**

Order number	376725 3
GTIN	4045197226792
Item class	32S

Description**Version:**

Hardened shoulder screws.

- **Ergonomic handle made of oil-resistant plastic.**

Application:

- **Direct fixing to sheet metal fixing points.**
- **Connected to jig body with threaded end of arm.**

Optional extras:

Angled base No. 376735.

Note:

- **Available in stainless steel on request.**

Technical description

thread at front of clamp	M20×1.5 mm
Clamping force P (pressure and traction)	1300 N
Clamping range	38 mm
Contact screw	M8×50 mm
Overall height H	100 mm
Overall length L	237 mm

Type	376725 3
Type of product	Push-pull toggle clamp

Accessories

Angled base sturdy Type 2	376735 2
Angled base sturdy Type 3	376735 3