



## Carrier jaw movable pivoting, for type: 125



### Order data

Order number	361336 125
GTIN	4250364402415
Item class	34A

### Description

#### Application:

Movable pivoting carrier jaw for compensation of non-parallel clamping faces, required for clamping unequal workpieces.

#### Suitable for:

Titan 2 No. 361302.

#### Note:

Wedge mountings + accessories No. 361341 – 361352, gripp inserts No. 361238 – 361250.

### Technical description

for type	125
Jaw width b	97 mm
c	24 mm
Jaw height h	20 mm
Jaw length l	189 mm
suitable for colour code	Titan2/TitanSense
suitable for colour code	LCV125G
Type of product	Vice jaws

---

**Accessories**

Mounting bolts 23 mm – 48 mm Overall height h 43 mm

361343 43

Mounting bolts 23 mm – 48 mm Overall height h 48 mm

361343 48