



Universal pull-down jaw, for T-Rex fixed, for type: 125



Order data

Order number	361228 125
GTIN	4250364402040
Item class	34A

Description

Version:**Capacities:**

High side **with** spring leaves

0 – 100 mm (T-Rex) / 0 – 138 mm (Centro Gripp).

High side **without** spring leaves

0 – 100 mm (T-Rex) / 0 – 156 mm (Centro Gripp).

Stepped side **without** spring leaves

44 – 126 mm (T-Rex) / 54 – 208 mm (Centro Gripp).

Application:

Pull-down with ground spring leaves for rough and machined surfaces. Click quick-change system for mounting click inserts. High clamping accuracy for parallel or right angle machining. Clamping faces leave virtually no visible impression.

Suitable for :

Fixed jaws for T-Rex No. 361202.

Supplied with:

Spring leaves.

Note:

Please order spring leaves separately!

Jaw width b: 124.4 mm

Width b₁: 90 mm

c: 14 mm

c₁: 19 mm

Jaw height h: 34 mm
Jaw length l: 59 mm

Technical description

c_1	19 mm
Length l_2	8.8 mm
for type	125
Width b_1	90 mm
Jaw width b	124.4 mm
c	14 mm
Jaw height h	34 mm
suitable for colour code	T-Rex
Jaw length l	59 mm
Type of product	Vice jaws