



Digital XTL internal quick measuring device, Measuring range: 20-25mm



Order data

Order number	428760 20-25
GTIN	2050001706454
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

Technical description

Scale divisions	0.001 mm
Standard measuring depth	66 mm
Measuring range	20 - 25 mm
Dimension a	0.5 mm
Measuring depth with extension	216 mm
Error limit	0.004 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 22 mm	484030 22
Receiver / USB keyboard interface Type	498965
Setting ring DIN 2250 C Nominal size \varnothing 24 mm	484030 24
Setting ring DIN 2250 C Nominal size \varnothing 20 mm	484030 20
Connection cable Duplex Type USB2	498950 USB2
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ring DIN 2250 C Nominal size \varnothing 25 mm	484030 25
Extension for internal micrometers Type 4/150	428510 4/150
Connection cable Duplex Type 2	498950 2
Multi-receiver / USB keyboard interface Type	498975