

**Universal pull-down jaw, for T-Rex / Centro Gripp movable, for type: 125****Order data**

Order number	361229 125
GTIN	4250364402057
Item class	34A

Description**Version:****Capacities:**

High side **with** spring leaves

0 – 100 mm (T-Rex) / 0 – 138 mm (Centro Gripp).

High side **without** spring leaves

0 – 100 mm (T-Rex) / 0 – 156 mm (Centro Gripp).

Stepped side **without** spring leaves

44 – 126 mm (T-Rex) / 54 – 208 mm (Centro Gripp).

Application:

Pull-down with ground spring leaves for rough and machined surfaces. Click quick-change system for mounting click inserts. High clamping accuracy for parallel or right angle machining. Clamping faces leave virtually no visible impression.

Supplied with:

Spring leaves.

Note:

Please order spring leaves separately!

Jaw width b: 90 mm

c: 12 mm

c₁: 34 mm

Jaw height h: 34 mm

Height h₁: 16 mm

Jaw length l: 61 mm

Technical description

Jaw height h	34 mm
c_1	34 mm
for type	125
Height h_1	16 mm
Length l_1	21 mm
suitable for colour code	Centro Gripp
suitable for colour code	T-Rex
c	12 mm
Length l_2	8.8 mm
Jaw length l	61 mm
Jaw width b	90 mm
Type of product	Vice jaws