



## Gripp jaw, for T-REX fixed, for type: 125



### Order data

Order number	361217 125
GTIN	4250364402293
Item class	34A

### Description

#### Version:

Rigid anti-vibration design for parts clamped upright. Additional clamping area, ground both sides.

#### Application:

For rectangular workpieces (saw-cut blanks)  $// \leq 0.5 \text{ mm}$

#### Suitable for:

Fixed jaws for T-Rex No. 361202.

### Technical description

for type	125
Height $h_2$	16 mm
$c_1$	34 mm
Step $s$	4 mm
Jaw height $h$	26 mm
Height $h_3$	14 mm
Height $h_1$	23 mm
Jaw length $l$	60.6 mm
$c$	14 mm
suitable for colour code	T-Rex

Jaw width b	118 mm
Type of product	Vice jaws