



Gripp jaw, for T-Rex / Centro Gripp movable, for type: 64



Order data

Order number	361218 64
GTIN	4250364402286
Item class	34A

Description

Version:

Rigid anti-vibration design for parts clamped upright. Additional clamping area, ground both sides.

Application:

For rectangular workpieces (saw-cut blanks) // ≤ 0.5 mm

Suitable for:

Movable jaws for T-Rex No. 361202 and Centro Gripp No. 361180.

Technical description

b_1	64 mm
c_1	22 mm
Height h_3	14 mm
Jaw height h	55 mm
c	12 mm
for type	64
Jaw length l	62.5 mm

Height h_2	35 mm
Height h_1	52 mm
Step s	4 mm
suitable for colour code	Centro Gripp
suitable for colour code	T-Rex
Jaw width b	96 mm
Type of product	Vice jaws