



## Digital XTL internal quick measuring device, Measuring range: 35-50mm



### Order data

Order number	428760 35-50
GTIN	2050001706478
Item class	46B

### Description

#### Version:

**3-point XT internal micrometer series** for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

#### Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

#### Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

#### Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

### Technical description

Standard measuring depth	80 mm
Dimension a	0.5 mm
Measuring range	35 - 50 mm
Measuring depth with extension	230 mm
Scale divisions	0.001 mm
Error limit	0.004 mm

Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

## Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50

## Accessories

Connection cable Duplex Type 2	498950 2
Setting ring DIN 2250 C Nominal size Ø 46 mm	484030 46
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ring DIN 2250 C Nominal size Ø 38 mm	484030 38
Multi-receiver / USB keyboard interface Type	498975
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
Connection cable Duplex Type USB2	498950 USB2
Setting ring DIN 2250 C Nominal size Ø 44 mm	484030 44
Receiver / USB keyboard interface Type	498965
Setting ring DIN 2250 C Nominal size Ø 42 mm	484030 42

Setting ringDIN 2250 C Nominal size Ø 45 mm	484030 45
Setting ringDIN 2250 C Nominal size Ø 50 mm	484030 50
Setting ringDIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ringDIN 2250 C Nominal size Ø 36 mm	484030 36
Extension for internal micrometers Type 4/150	428510 4/150