



Hook toggle clamp vertical, Type: 2



Order data

Order number	376820 2
GTIN	4020772008642
Item class	35A

Description

Version:

- **Quick-action clamp with toggle action.**
- **Self-locking mechanism prevents inadvertent opening.**
- **Rivet of stainless steel.**
- **Handle made of oil-resistant plastic.**
- **Galvanised clamps.**
- **Clamping hook adjustable using thread.**
- **Bearing bushes case-hardened.**
- **Bearings greased.**
- **Hardened hook.**

Complete with catch.

Application:

For closing containers.

Note:

- **More compact design due to new handle.**
- **Ergonomic 2-component handle, very comfortable to use due to enlarged hand rest.**

Technical description

Adjustment travel of clamping hook c	5 - 28 mm
Bore \varnothing d	5.2 mm
Clamping force P (traction)	1600 N
Hole spacing f	19.5 - 23.5 mm
Hole spacing e	13 mm
Clamping height h	12 mm
Overall height H	47 mm
Overall length L	91 mm
Type	6848VJ
Type of product	Hook toggle clamp