



Gripp jaw, for T-Rex / Centro Gripp movable, for type: 125



Order data

Order number	361218 125
GTIN	4250364402309
Item class	34A

Description

Version:

Rigid anti-vibration design for parts clamped upright. Additional clamping area, ground both sides.

Application:

For rectangular workpieces (saw-cut blanks) // ≤ 0.5 mm

Suitable for:

Movable jaws for T-Rex No. 361202 and Centro Gripp No. 361180.

Technical description

c	14 mm
c ₁	34 mm
Height h ₃	14 mm
Height h ₂	16 mm
Jaw height h	26 mm
for type	125
Jaw length l	60.6 mm
Height h ₁	23 mm
Step s	4 mm

suitable for colour code	Centro Gripp
suitable for colour code	T-Rex
Jaw width b	118 mm
Type of product	Vice jaws